



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Power Supply

**PSG60N24RP**

**UPC:**786685757667

### Dimensions:

- **Height:** 4.696 IN
- **Length:** 4.748 IN
- **Width:** 1.259 IN

**Weight:**.66 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** NEC Class II
- **Wattage:** 60W
- **Phase:** Single-phase
- **Voltage Rating:** 24 Vdc

### Supporting documents:

- [Eatons PSG Series Power Supplies](#)
- [PSG60N24RP 3D Model Xchange](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Installation Instructions for PSG60F Power Supply](#)
- [PSG60N24RP 2D Drawing Xchange](#)
- [Eaton Specification Sheet - PSG60N24RP](#)
- [PSG60N24RP 2D PDF](#)
- [PSG60N24RP 3D Inventor](#)
- [PSG60N24RP AutoCAD 2D Footprint \(mm\)](#)
- [PSG60N24RP AutoCAD 2D Footprint](#)

### Certifications:

- CSA Certified
- UL Listed



- cUL Listed
- EN 60204
- EN 61000-4-11
- EN 610003-2
- EN 61000-4-2
- EN 61000-406
- UL 508
- EN 50178
- EN 61000-6-2
- IEC Rated
- PELV (EN 60204)
- EN 61000-6-3
- cRUus
- UL Listed file 60950-1
- SELV (EN 60950)

**Product compliance:**

- CE Marked
- German Safety
- RoHS Compliant
- DIN 57100-410