



Powering Business Worldwide

pe.eaton.com

Molded Case Engine Generator Circuit Breaker

JG3250S41

UPC:782116018741

Dimensions:

- **Height:** 6 IN
- **Length:** 12 IN
- **Width:** 7 IN

Weight:9.21 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 250A
- **Number Of Poles:** Three-pole
- **Series:** Series C
- **Shunt Trip:** 12-24 Vac/dc left pigtail same side
- **Terminals:** Line and load
- **Trip Type:** Thermal magnetic
- **Feed Type:** Reverse
- **Frame:** JG-frame
- **Generator Rating:** 90 kVA/72 kW at 240V, 181 kVA/144 kW at 480V, 226 kVA/181 kW at 600V
- **Pickup:** 350-700

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Series C Engine Generator Circuit Breakers - Dimension Sheets](#)
- [Eaton Specification Sheet - JG3250S41](#)

Certifications:

- CSA Certified
- IEC 947-2



- UL 489
- UL Listed
- CSA Std. C22.2 No. 5
- IEC Rated

Product compliance: No Data

© 2016 Eaton. All rights reserved.