



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## SVX Independent Drives

**SVX040A2-4A1N1**

**UPC:**782116011711

### Dimensions:

- **Height:** 24.8 IN
- **Length:** 10.1 IN
- **Width:** 9.3 IN

**Weight:**77.2 LB

### Warranties:

- 2 year

### Specifications:

- **Brake Chopper:** No brake chopper
- **Input:** Three-phase, EMC H
- **Keypad:** Alphanumeric
- **Modification:** Standard boards
- **Frame Size:** FR7
- **Horsepower:** 40 hp
- **Rating:** NEMA Type 12/IP54
- **Software:** Standard Software
- **Voltage Rating:** 480V

### Supporting documents:

- [9000X AFD User Manual](#)
- [SVX\\_\(FR7\) 2D PDF](#)
- [SVX\\_\(FR7\) 3D Model Xchange](#)
- [SVX\\_\(FR7\) 3D Inventor](#)
- [Product Datasheet - SVX040A2-4A1N1](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [SVX9000 Adjustable Frequency Drives Brochure](#)
- [SVX9000 Adjustable Frequency Drives Product Aid](#)
- [Eaton Specification Sheet - SVX040A2-4A1N1](#)



- [SVX\\_\(FR7\) AutoCAD 2D Footprint](#)
- [SVX\\_\(FR7\) AutoCAD 2D Footprint \(mm\)](#)
- [SVX\\_\(FR7\) 2D Drawing Xchange](#)

**Certifications:**

- IEC 61800-2
- UL 508C
- EN 61800-3 Level H

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.