



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E57 Global Series Tubular Inductive Proximity Sensor

**E57-30GE15-CDB**

**UPC:**786685125190

### Dimensions:

- **Height:** 3.11 IN
- **Length:** 1.18 IN
- **Width:** 1.18 IN

**Weight:**.375 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 100 mA at 30 Vdc
- **Contact Configuration:** NPN Open Collector, Normally Open
- **Diameter:** 1.18 IN
- **Enclosure Material:** Nickel Plated Brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-30GE15-CDB](#)

**Certifications:** No Data



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.