



Powering Business Worldwide

pe.eaton.com

M-Max Series Adjustable Frequency

MMX34AA038F0-0

UPC:786685626703

Dimensions:

- **Height:** 14.57 IN
- **Length:** 6.5 IN
- **Width:** 8.07 IN

Weight:17 LB

Notes:Please consult factory for extended warranty options.

Warranties:

- Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

Specifications:

- **Options:** Full Version
- **Output Current:** 38 A
- **Enclosure:** IP20
- **Frame Size:** FS5
- **Horsepower:** 25 hp
- **Nominal Ac Current:** 38A
- **Phase:** Three-phase
- **Protection Filtering:** EMC Category C2 C3 and C4 (Level H) with an internal RFI filter option
- **Software:** AA
- **Voltage Rating:** 380–480V three-phase in 460V three-phase out

Supporting documents:

- [Eaton's Volume 6-Solid-State Motor Control](#)



- [M-Max Series adjustable frequency drives](#)
- [User Manual, M-Max Series Adjustable Frequency Drive](#)
- [Variable frequency drive - Product overview](#)
- [MMX_\(FR5\) 2D Drawing Xchange](#)
- [Eaton Specification Sheet - MMX34AA038F0-0](#)
- [MMX_\(FR5\) 2D PDF](#)
- [MMX_\(FR5\) 3D Model Xchange](#)

Certifications:

- EN 61800-5-1
- IEC Rated
- UL Listed
- EN 60204-1
- cUL Listed
- EN 61800-3

Product compliance:

- EMC Category C2, C3, and C4 (Level H): With an internal RFI filter option