



Powering Business Worldwide

pe.eaton.com

Limit Switch Receptacle

E50RAS20

UPC:782113472782

Dimensions:

- **Height:** 1.06 IN
- **Length:** 2.92 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Cable Type:** SOOW-J
- **Cord Length:** 240 FT
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67
- **Operating Temperature:** 10° to 200°F
- **Series:** E50
- **Switch Type:** Pre-wired cable

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50RAS20](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

