



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## SPX Adjustable Frequency Drive

**SPX300A0-4A2N1U**

**UPC:**786685100944

### Dimensions:

- **Height:** 45.9 IN
- **Length:** 19.9 IN
- **Width:** 19.7 IN

**Weight:**518 LB

**Notes:**Please consult factory for extended warranty options.

### Warranties:

- Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

### Specifications:

- **Keypad:** Alphanumeric
- **Options:** Standard boards
- **Enclosure:** Open chassis
- **Frame Size:** FS10
- **Horsepower:** 300 hp
- **Phase:** Three-phase
- **Protection Filtering:** EMC N
- **Software:** Standard software
- **Voltage Rating:** 480V

### Supporting documents:

- [Eaton's Volume 6-Solid-State Motor Control](#)
- [SVX and SPX Series FR4-FR11 PDF Open Drawings](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - SPX300A0-](#)



## 4A2N1U

- [Product Datasheet - SPX300A0-4A2N1U](#)

### **Certifications:**

- IEC 61800-2
- UL 508C
- UL Listed
- EN 61800-3

### **Product compliance:**

- Fulfills all EMC immunity requirements
- CE Marked