



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series G, EG-frame Molded Case Circuit Breaker

EGH3125FFB

UPC:786685381954

### Dimensions:

- **Height:** 5.5 IN
- **Length:** 2.99 IN
- **Width:** 3 IN

**Weight:**3 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 125A
- **Interrupt Rating:** 100 kAIC at 240V, 70 kAIC at 415V, 65 kAIC at 480V, 35 kAIC at 600Y/347V
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600Y/347V
- **Frame Size:** EG-frame
- **Series:** Series G
- **Terminals:** Bolt-on
- **Trip Type:** Fixed thermal, fixed magnetic

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - EGH3125FFB](#)

### Certifications:

- CSA Certified
- IEC Rated
- UL Listed

### Product compliance:



- CE Marked

---

© 2016 Eaton. All rights reserved.