



Powering Business Worldwide

pe.eaton.com

CN35 or A202 Enclosed Lighting Contactor

ECL03E2C3A

UPC:782114319130

Dimensions:

- **Height:** 30.44 IN
- **Length:** 15.38 IN
- **Width:** 12.75 IN

Weight:60 LB

Notes:Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 100A
- **Coil Voltage:** 440V/50 Hz, 480V/60 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Frame Size:** 90 mm
- **Number Of Poles:** Three-pole
- **Type:** Non-combination electrically held

Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03E2C3A](#)

Certifications:

- UL Listed
- cUL Listed

Product compliance: No Data

