



Powering Business Worldwide

pe.eaton.com

Magnetic Shoe Brake

511H993-41

UPC:782113139845

Dimensions:

- **Height:** 7.1 IN
- **Length:** 7.1 IN
- **Width:** 10.3 IN

Weight:30.1 LB

Notes:Intermittent duty indicates that the coil can be placed across the line continuously for one hour maximum without excessive heating. It is equivalent to 1/2 time On and 1/2 time Off. Does not include wheel.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Coil Voltage:** 480 Vac
- **Frequency Rating:** 60 Hz
- **Mounting:** Floor mount
- **Torque Rating:** Intermittent: 35 lbs
- **Type:** Type S

Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Eaton Specification Sheet - 511H993-41](#)

Certifications: No Data

Product compliance: No Data

