



Powering Business Worldwide

pe.eaton.com

Molded Case Engine Generator Circuit Breaker

NG3700WS03Z01

UPC:782116078677

Dimensions:

- **Height:** 16.5 IN
- **Length:** 6 IN
- **Width:** 11.8 IN

Weight:44 LB

Warranties: No Data

Specifications:

- **Amperage Rating:** 700A
- **Number Of Poles:** Three-pole
- **Feed Type:** Reverse
- **Frame:** NG-frame
- **Generator Rating:** 253 kVA/202 kW at 249V, 505 kVA/404 kW at 480V, 632 kVA/505 kW at 600V
- **Pickup:** 500-2500
- **Series:** Series C
- **Shunt Trip:** 12-24 Vac/dc left pigtail opposite
- **Terminals:** Line and load
- **Trip Type:** 310+

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - NG3700WS03Z01](#)

Certifications:

- UL 489
- CSA Std. C22.2 No. 5
- IEC 947-2

Product compliance: No Data



