



Powering Business Worldwide

pe.eaton.com

Rotary Disconnects

ER53060UD

UPC:786685466064

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:NEMA Type 12 enclosures (16–80A) can be field modified to meet NEMA Type 3R rainproof requirements when a factory-provided drain hole is opened.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 60A
- **Enclosure:** NEMA 12
- **Enclosure Material:** Painted galvanized steel
- **Max Hp Rating:** 15 at 208 Vac, 15 at 240 Vac, 30 at 480 Vac, 30 at 600 Vac
- **Number Of Poles:** Three-pole
- **Product Category:** Enclosed Rotary Non-Fusible
- **Series:** R-Series
- **Voltage Rating:** 600V

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - ER53060UD](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



