



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57SAL12A2S5

UPC:782116031047

Dimensions:

- **Height:** .47 IN
- **Length:** 2.46 IN
- **Width:** .47 IN

Warranties:

- 1 year

Specifications:

- **Type:** Inductive Proximity Sensor
- **Accuracy:** <1% sensing range
- **Contact Rating:** 250 mA at 40-240 Vac/20-250 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC/DC, NO
- **Cord Length:** 196.8 FT
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 40-250 Vac 50/60 Hz, 20-250 Vdc
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Resettable S/C, overload
- **Series:** E57

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57SAL12A2S5](#)

Certifications: No Data

Product compliance: No Data



