



Powering Business Worldwide

pe.eaton.com

E50 Heavy Duty Factory Sealed 6P+ Limit Switch

E50ALT16P

UPC:782113727417

Dimensions:

- **Height:** 5.06 IN
- **Length:** 1.54 IN
- **Width:** 1.58 IN

Weight:2.1 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** Within 0.002
- **Connection:** 8 Ft. (2.5m) Cable
- **Contact Rating:** 10A at 240Vac, 1A at 125Vdc
- **Cable Type:** SOOW-A
- **Contact Configuration:** 1NO-1NC
- **Cord Length:** 96 FT
- **Enclosure Material:** Die Cast Zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Led Indicators:** LED (24–120 Vac/dc)
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** 14° to 221°F (-10° to 105°C)
- **Switch Type:** Top Push Button

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50ALT16P](#)

Certifications:

- UL Listed
- CSA Certified



Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.