



Powering Business Worldwide

pe.eaton.com

Series C, F-frame Molded Case Circuit Breaker

HFD3040S06

UPC:782114197394

Dimensions:

- **Height:** 6 IN
- **Length:** 3.38 IN
- **Width:** 4.13 IN

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 40A
- **Number Of Poles:** Three-pole
- **Frame Size:** F-frame
- **Series:** Series C
- **Shunt Trip:** 48-127 Vac or 48-60 Vdc left pigtail rear
- **Trip Type:** Thermal magnetic

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Counterfeit and Gray Market Awareness Guide](#)
- [MOEM MCCB Product Selection Guide](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers](#)
- [Eaton Specification Sheet - HFD3040S06](#)

Certifications:

- UL Listed

Product compliance: No Data



