



Powering Business Worldwide

pe.eaton.com

Molded Case Circuit Breakers Replacement Products

2605D15G19

UPC:786679935200

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes: 120V suitable for 55% pickup for ground fault applications. Not field mountable on non-automatic breakers/molded case switches. Field mounting voids UL listing except on LA,HLA,MA,HMA,NB,HNB,PB,KB,HKB,KA,HKA,LB,HLB and SELTRONIC breakers.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Field mounting shunt trip
- **Voltage Rating:** 120V
- **Frequency Rating:** 50-60 Hz
- **Mounting:** Right-hand
- **Used With:** JA, KA, HKA, DA, LB, LBB, HLB breakers

Supporting documents:

- [E2 Mining Series Sales Brochure](#)
- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - 2605D15G19](#)

Certifications:

- UL Listed

Product compliance: No Data



