



Powering Business Worldwide

pe.eaton.com

Spring Cage Connection Multi-Conductor Terminal Blocks

XBPT25D22

UPC:782116905645

Dimensions:

- **Height:** .2 IN
- **Length:** 2.83 IN
- **Width:** .2 IN

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** IEC 28A, EN 24,21A, UL 20A
- **Color:** Gray
- **Maximum Wire Size:** 12 AWG/2.5 mm²
- **Number Of Wires:** Four-wire
- **Quantity:** 50
- **Voltage Rating:** IEC 800V, EN 550V, UL 600V
- **Wire Size:** IEC #28-12 AWG, EN #24-12, UL #26-12 AWG

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XB IEC TERMINAL BLOCKS](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBPT25D22](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data



