



Powering Business Worldwide

pe.eaton.com

Limit Switch Body

E50SB6P

UPC:782113137056

Dimensions:

- **Height:** 2.46 IN
- **Length:** 3.63 IN
- **Width:** 1.54 IN

Warranties:

- 1 year

Specifications:

- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Cable Type:** SOOW-J
- **Contact Configuration:** 2NO-2NC
- **Cord Length:** 96 FT
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** -31° to 175°F
- **Series:** E50

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SB6P](#)

Certifications:

- CSA Certified
- UL Recognized

Product compliance: No Data

