



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Series G, NG-frame Molded Case Circuit Breaker

NGC312032EC

UPC:786685574424

### Dimensions:

- **Height:** 16 IN
- **Length:** 5.5 IN
- **Width:** 8.25 IN

**Weight:**45 LB

**Notes:**All Eaton NG-Frame circuit breakers are suitable for reverse feed use, Breakers do not ship with lugs

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 1200A
- **Interrupt Rating:** 100 kA
- **Number Of Poles:** Three-pole
- **Frame Size:** NG-frame
- **Rating:** 100% rated
- **Series:** Series G
- **Terminals:** Imperial tapped line and load
- **Trip Type:** 310+ electronic LSI

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Instruction Leaflet for Drawout Cassette for NG Frame Circuit Breakers](#)
- [J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)
- [Eaton Specification Sheet - NGC312032EC](#)



**Certifications:**

- CSA Certified
- UL Listed

**Product compliance:**

- HACR Rated

---

© 2016 Eaton. All rights reserved.