



Powering Business Worldwide

pe.eaton.com

Series G, NG-frame Molded Case Circuit Breaker

NGC308032EC

UPC:786685574387

Dimensions:

- **Height:** 16 IN
- **Length:** 5.5 IN
- **Width:** 8.25 IN

Weight:45 LB

Notes:All Eaton NG-Frame circuit breakers are suitable for reverse feed use, Breakers do not ship with lugs

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete breaker
- **Amperage Rating:** 800A
- **Interrupt Rating:** 100 kA
- **Number Of Poles:** Three-pole
- **Frame Size:** NG-frame
- **Rating:** 100% rated
- **Series:** Series G
- **Terminals:** Imperial tapped line and load
- **Trip Type:** 310+ electronic LSI

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Instruction Leaflet for Drawout Cassette for NG Frame Circuit Breakers](#)
- [J-Frame 310+ and L-Frame 310+ Molded-case circuit breakers](#)
- [Eaton Specification Sheet - NGC308032EC](#)



Certifications:

- CSA Certified
- UL Listed

Product compliance:

- HACR Rated

© 2016 Eaton. All rights reserved.