



Powering Business Worldwide

pe.eaton.com

3/4 in Type CH Solar Power Center Meter Breaker

CMBX3242PV200TS

UPC:786685690179

Dimensions:

- **Height:** 6 IN
- **Length:** 36 IN
- **Width:** 24 IN

Weight:45 LB

Notes:Xcel approved

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Over/under construction
- **Type:** CH solar-ready
- **Amperage Rating:** 200A
- **Bus Material:** Copper
- **Bus Rating:** 225 A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Galvanized steel
- **Feed Type:** Overhead/underground
- **Input:** 70 max PV input
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** CSR
- **Mounting:** Surface mounting
- **Number Of Circuits:** 42
- **Number Of Sockets:** 1
- **Number Of Spaces:** 32
- **Phase:** Single-phase
- **Used With:** Type CH breakers
- **Voltage Rating:** 120/240V
- **Box Size:** 14
- **Bypass:** Lever bypass

Supporting documents:



- Eaton's Volume 15-Solar Inverters and Electrical Balance of System
- Solar power centers
- Eaton Specification Sheet - CMBX3242PV200TS

Certifications:

- UL Listed

Product compliance: No Data

© 2016 Eaton. All rights reserved.