



Powering Business Worldwide

pe.eaton.com

E10 Series Light Industrial Toggle Switch

E10P115JS

UPC:782113699905

Dimensions:

- **Height:** .5 IN
- **Length:** 6 IN
- **Width:** 5 IN

Weight:.05 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Pushbutton Actuator
- **Bushing Length:** 0.34 inch bushing
- **Button Extension:** 0.25 inch button extension
- **Max Op Force:** 0.9 lbs
- **Number Of Poles:** Single-pole
- **Operating Mode:** Momentary
- **Rating:** 15A at 125 Vac (NO), 10A at 250 Vac (NO), 1/3 hp at 125-250 Vac
- **Series:** E10
- **Terminals:** Screw
- **Throw Type:** Single-throw

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - E10P115JS](#)

Certifications:

- CSA Certified
- UL Recognized



Product compliance: No Data

© 2016 Eaton. All rights reserved.