



Powering Business Worldwide

pe.eaton.com

E52 Rectangular Style Inductive Proximity Sensor

E52RAL12T111

UPC:782113942346

Dimensions:

- **Height:** 1.18 IN
- **Length:** .47 IN
- **Width:** .28 IN

Weight:.0438 LB

Warranties:

- 1 year

Specifications:

- **Connection:** 6.6 Ft. (2m) Cable
- **Contact Rating:** 100 mA at 30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** PNP Open Collector, Normally Closed
- **Cord Length:** 79.2 FT
- **Enclosure Material:** PBT composition
- **Environmental Rating:** NEMA 1, 2, 3, 3S, 4, 12 (IP66)
- **Input Voltage:** 12-24 Vdc
- **Led Indicators:** Output Status
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** 14° to 131°F (-10° to 55°C)
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E52RAL12T111](#)

Certifications: No Data

Product compliance: No Data



