



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Mini-Power Center

**P29G11S10CUB**

**UPC:**786680090875

### Dimensions:

- **Height:** 40.85 IN
- **Length:** 11.82 IN
- **Width:** 13.47 IN

**Weight:**290 LB

**Notes:**All copper construction (coil and interior) and accepts bolt-on branch breakers from the BAB family

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** Mini-power center
- **Coil Material:** Copper windings
- **Enclosure:** NEMA 3R
- **Frame:** 308
- **Frequency Rating:** 60 Hz
- **Phase:** Single-phase
- **Primary Voltage:** 208V
- **Secondary Voltage:** 120/240V
- **Tap Size:** 2 at -5% FCBN
- **Temperature Rating:** 115°C
- **Volt Ampere Rating:** 10 KVA
- **Weathershield:** Indoor-Outdoor
- **Wiring Connection:** 109A10K

### Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Eaton Specification Sheet - P29G11S10CUB](#)

### Certifications:



- ANSI
- IEEE Certified
- UL Listed

**Product compliance:**

- NEMA Compliant

---

© 2016 Eaton. All rights reserved.