



Powering Business Worldwide

pe.eaton.com

## CurrentWatch Series Current Transducer

**EACR2420SP**

**UPC:**786685120720

### Dimensions:

- **Height:** 3.53 IN
- **Length:** 2.25 IN
- **Width:** 1.19 IN

**Weight:**.25 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** 1% FS
- **Connection:** Screw Terminals
- **Enclosure Material:** UL94 V0 Flammability Rated Plastic
- **Input Voltage:** 24Vdc Current Loop
- **Led Indicators:** No
- **Maximum Ac Current:** Measure up to 200A
- **Operating Temperature:** -4° to 122°F (-20° to 50°C)
- **Switch Type:** Current Sensor

### Supporting documents:

- [CurrentWatch current sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - EACR2420SP](#)

**Certifications:** No Data

**Product compliance:** No Data

