



Powering Business Worldwide

pe.eaton.com

Solar DC Disconnect for Ungrounded PV Systems

DCU2064FRM

UPC:786685625157

Dimensions:

- **Height:** 11.5 IN
- **Length:** 37.5 IN
- **Width:** 19 IN

Weight:45 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** DC disconnect/ungrounded system
- **Amperage Rating:** 200A
- **Main Lug Wire Size:** LC: In 300 MCM-#6 out 300 MCM-#6. SR: in 300 MCM-#6 out 300 MCM-#6. EG: in #4-#14 AWG out 1/0-#14
- **Maximum Voltage:** 600 Vdc
- **Nema Rating:** NEMA 3R
- **Number Of Circuits:** 2
- **Protection:** Fusible
- **Switch Type:** DC photovoltaic systems
- **System Voltage:** 600 Vdc per pole

Supporting documents:

- [DC disconnects for grounded and ungrounded photovoltaic installations](#)
- [Eatons Volume 15-Solar Inverters and Electrical Balance of System](#)
- [Eaton Specification Sheet - DCU2064FRM](#)

Certifications:

- NEC 690 per UL 1741



- UL 98B

Product compliance: No Data

© 2016 Eaton. All rights reserved.