



Powering Business Worldwide

pe.eaton.com

Solar DC Disconnect

DCU3062FRM

UPC:786685557465

Dimensions:

- **Height:** 9 IN
- **Length:** 25.5 IN
- **Width:** 13.25 IN

Weight:40 LB

Notes:Not all configurations for ampere rating and number of circuits are available. All circuit configurations can be found in the product dimension tables.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** For Ungrounded PV Systems
- **Type:** DC disconnect/ungrounded system
- **Amperage Rating:** 60A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Configuration:** Fusible
- **Ground:** Ungrounded
- **Main Lug Wire Size:** #14-#2 AWG lug capacity, #14-1/0 AWG solid return
- **Number Of Circuits:** 3 circuits
- **Series:** DC Photovoltaic Applications
- **Voltage Rating:** 600 Vdc
- **Wire Size:** #14-#4 AWG input grd., #14-#4 AWG output grd.

Supporting documents:



- DC disconnects for grounded and ungrounded photovoltaic installations
- Eatons Volume 15-Solar Inverters and Electrical Balance of System
- Eaton Specification Sheet - DCU3062FRM

Certifications:

- NEC 690 per UL 1741
- UL 98B

Product compliance: No Data

© 2016 Eaton. All rights reserved.