



Powering Business Worldwide

pe.eaton.com

E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor

E51CNP6

UPC:782113214849

Dimensions:

- **Height:** 4.89 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

Weight:.975 LB

Notes:Assembled sensor with head; sensor body and receptacle. Logic modules must be ordered separately.

Warranties:

- 3 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 1.0A Solid State Output
- **Contact Configuration:** L1 Switched, N.O. and N.C.
- **Enclosure Material:** Receptacle: Die Cast Zinc, Body and Head: Plastic
- **Environmental Rating:** NEMA 4, 4X, 13
- **Input Voltage:** 120 Vac
- **Maximum Ac Current:** 1.0A
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51CNP6](#)

Certifications:



- UL Listed
- CSA Certified

Product compliance: No Data

© 2016 Eaton. All rights reserved.