



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Premium+ Inductive Proximity Sensor

E57LAL12T111ED

UPC:782113605029

### Dimensions:

- **Height:** .47 IN
- **Length:** 3.06 IN
- **Width:** .47 IN

### Warranties:

- 1 year

### Specifications:

- **Type:** Premium+ Inductive Proximity Sensor
- **Accuracy:** <3%
- **Connection:** M12
- **Contact Rating:** 500 mA at 6-30 Vdc
- **Contact Configuration:** NO PNP open collector
- **Diameter:** .472440948 MM
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** 360° viewable LED
- **Maximum Dc Current:** 500 mA
- **Number Of Pins:** 4 pin
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Auto reset
- **Series:** E57

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL12T111ED](#)

### Certifications:



- CSA Certified
- UL Listed

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.