



Powering Business Worldwide

pe.eaton.com

House Panel

HP404040SHFA

UPC:782116959976

Dimensions:

- **Height:** 7.5 IN
- **Length:** 45 IN
- **Width:** 31 IN

Weight:155 LB

Notes:Includes manual bypass and additional ground lug to meet Nevada requirements. Load conductors can exit the top, bottom, side or back. Secondary breaker not included.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Amperage Rating:** 400A
- **Bus Material:** Aluminum
- **Bypass:** Manual bypass
- **Enclosure:** NEMA 3R
- **Feed Type:** Underground
- **Interrupt Rating:** 22 kAIC
- **Line:** Lug landings for compression, lugs not included
- **Main Circuit Breaker:** CSR2200
- **Mounting:** Semi-flush mounting
- **Number Of Circuits:** 40
- **Number Of Sockets:** 1
- **Secondary Circuit Breaker:** BRH/BWH
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V



Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - HP404040SHFA](#)

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.