



Powering Business Worldwide

pe.eaton.com

Quicklag Industrial Thermal-Magnetic Circuit Breaker

BAB1050S

UPC:786679368824

Dimensions:

- **Height:** 4.8 IN
- **Length:** 3.7 IN
- **Width:** 1.2 IN

Weight:.3 LB

Warranties:

- 1 year

Specifications:

- **Amperage Rating:** 50A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 240V
- **Trip Type:** Non-interchangeable
- **Mounting:** Bolt-on mount
- **Shunt Trip:** 120-240V

Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Eaton Specification Sheet - BAB1050S](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

