



Powering Business Worldwide

pe.eaton.com

E57 Premium+ Series Tubular Inductive Proximity Sensor

E57LAL12A2S5

UPC:782113856711

Dimensions:

- **Height:** 2.46 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight:.225 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 16 Ft. (5m) Cable
- **Contact Rating:** 250 mA at 250Vac
- **Cable Type:** PVC
- **Contact Configuration:** 2 - Wire AC, Normally Open
- **Cord Length:** 192 FT
- **Diameter:** .47 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 20-250 Vac
- **Led Indicators:** Red output status
- **Maximum Ac Current:** 250 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** None
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL12A2S5](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.