



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Limit Switch Body

E50SAL6P

UPC:782113726632

### Dimensions:

- **Height:** 2.46 IN
- **Length:** 4.93 IN
- **Width:** 1.54 IN

### Warranties:

- 1 year

### Specifications:

- **Contact Rating:** 10A at 240 Vac, 1A at 250 Vdc
- **Cable Type:** SOOW-J
- **Contact Configuration:** 1NO-1NC
- **Cord Length:** 96 FT
- **Enclosure Material:** Die cast zinc
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Led Indicators:** LED indicator
- **Light Unit Voltage:** 24-120 Vac/dc
- **Maximum Ac Current:** 10A
- **Maximum Dc Current:** 1A
- **Operating Temperature:** -31° to 175°F
- **Series:** E50 Heavy Duty Factory Sealed 6P+

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50SAL6P](#)

### Certifications:

- UL Recognized
- CSA Certified

**Product compliance:** No Data



