



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E57 Premium+ Series Tubular Inductive Proximity Sensor

**E57-18LE20-BB**

**UPC:**782113949215

### Dimensions:

- **Height:** 3.39 IN
- **Length:** .71 IN
- **Width:** .71 IN

**Weight:**.1438 LB

### Warranties:

- 1 year

### Specifications:

- **Accuracy:** < 3% of sensing distance
- **Connection:** 4 Pin Mini Connector
- **Contact Rating:** 500 mA at 6-30 Vdc, 300 mA at 32-48 Vdc
- **Contact Configuration:** PNP, Normally Open
- **Diameter:** .71 IN
- **Enclosure Material:** Tube: Stainless Steel, End Bell: Polycarbonate, Front Cap: Polyphenylene Sulfide
- **Environmental Rating:** NEMA 4,4X,6,6P,12,13,IP67,IP69K
- **Input Voltage:** 6-48 Vdc
- **Led Indicators:** Green power up turns red when output energized
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Non-embeddable
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Auto reset short circuit
- **Sensor Type:** Inductive Proximity

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)



- [Eaton Specification Sheet - E57-18LE20-BB](#)

**Certifications:**

- UL Listed
- CSA Certified

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.