



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Photoelectric Sensor

1456A-6503

UPC:782114106747

### Dimensions:

- **Height:** 1.64 IN
- **Length:** 3.19 IN
- **Width:** 1.83 IN

Notes:0

### Warranties:

- 3 year

### Specifications:

- **Connection:** Mini
- **Contact Rating:** 300 mA AC/DC at 20-264 Vac/15-30 Vdc
- **Output:** Solid-state
- **Contact Configuration:** AC: L1 switched, DC: NPN open collector
- **Enclosure Material:** Noryl
- **Environmental Rating:** NEMA 1, 3, 4, 12, 13
- **Input Voltage:** 20-264 Vac/15-30 Vdc
- **Led Indicators:** Output status
- **Maximum Ac Current:** 300 mA
- **Number Of Pins:** 3 pin
- **Operating Mode:** Light
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Sensor Type:** Polarized Retroreflective

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 1456A-6503](#)
- [Photoelectric sensors](#)

### Certifications:

- UL Listed
- CSA Certified



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.