



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## CN35 or A202 Enclosed Lighting Contactor

**ECL03F1A2A**

**UPC:**782114017029

### Dimensions:

- **Height:** 28.313 IN
- **Length:** 13.188 IN
- **Width:** 11.563 IN

**Weight:**41 LB

**Notes:**Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

### Warranties:

- 1 year

### Specifications:

- **Amperage Rating:** 200A
- **Coil Voltage:** 110V/50 Hz, 120V/60 Hz
- **Enclosure:** NEMA 1
- **Enclosure Material:** Painted steel
- **Number Of Poles:** Two-pole
- **Type:** Non-combination electrically held

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Lighting contactors](#)
- [Eaton Specification Sheet - ECL03F1A2A](#)

### Certifications:

- UL Listed
- cUL Listed

**Product compliance:** No Data

