



Powering Business Worldwide

pe.eaton.com

E57 Premium+ Series Tubular Inductive Proximity Sensor

E57LAL12T110E5

UPC:782113844305

Dimensions:

- **Height:** 2.87 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight:.2656 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 3%
- **Connection:** 16 Ft. (5m) Cable
- **Contact Rating:** 500 mA at 6-30Vdc
- **Cable Type:** PVC
- **Contact Configuration:** Normally Open NPN
Open Collector
- **Cord Length:** 192 FT
- **Diameter:** .47 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** IP67, IP69K, UL Type 1, NEMA 6P, 4X
- **Input Voltage:** 6–48 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 500 mA
- **Operating Mode:** Un-shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eaton's Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL12T110E5](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.