



Powering Business Worldwide

pe.eaton.com

Inductive Global Proximity Sensor

E57-30GE25-D

UPC:782116072705

Dimensions:

- **Height:** 1.18 IN
- **Length:** 2.17 IN
- **Width:** 1.18 IN

Weight:.62 LB

Warranties:

- 1 year

Specifications:

- **Type:** E57
- **Accuracy:** <2.0% sensing range
- **Contact Rating:** 100 mA at 10-30 Vdc
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire DC, NO
- **Cord Length:** 79.2 FT
- **Enclosure Material:** Nickel plated brass
- **Environmental Rating:** IP67, IP69K
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Output ON
- **Maximum Dc Current:** 100 mA
- **Operating Mode:** Unshielded
- **Operating Temperature:** 32° to 104°F
- **Protection:** S/C

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Global Series inductive proximity sensors](#)
- [Eaton Specification Sheet - E57-30GE25-D](#)

Certifications: No Data

Product compliance: No Data



