



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 22.5 mm, Non-metallic, Selector Switch Operator

E22K62

UPC:782113802688

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**Key Removal from Maintained Position Only. Will accept a maximum of 2 contact blocks (4 circuits) with supplied 3-way mounting adapter. Optional 5-way adapter will accept a maximum of 5 contact blocks (10 circuits)

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Key
- **Actuator Color:** None (key operator)
- **Bezel:** Chrome
- **Cam Code:** Cam 2
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Non-illuminated
- **Key Removal Position:** Left only
- **Number Of Positions:** Two-position
- **Series:** E22
- **Throw Type:** 45° Throw

### Supporting documents:

- [Eatons Volume 12-Aftermarket, Renewal Parts and Life Extension Solutions](#)
- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)



- [Eaton Specification Sheet - E22K62](#)

**Certifications:**

- IEC 947-5-1 MTTA
- UL 508
- CSA Certified
- Lloyd's Register Certified

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.