



Powering Business Worldwide

pe.eaton.com

E50 Series Limit Switch Operator

E50KL535

UPC:782113320120

Dimensions:

- **Height:** 1.52 IN
- **Length:** .69 IN
- **Width:** 1.5 IN

Weight:.09 LB

Notes:Lever length is from the operating shaft axis to the roller axis. Maximum roller length dimension between operating shaft axis to the roller axis for comparison. Precision adjustable to lesser dimensions.

Warranties:

- 1 year

Specifications:

- **Enclosure Material:** Lever: Aluminum, Roller: Steel Ball Bearing
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Operating Temperature:** -40° to 201°F (-40° to 94°C)
- **Switch Type:** Lever for Side Rotary Switches

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL535](#)

Certifications: No Data

Product compliance: No Data

