



Powering Business Worldwide

pe.eaton.com

H-Max Drive

HMX014A4NA

UPC:786685568218

Dimensions:

- **Height:** 13.22 IN
- **Length:** 37.3 IN
- **Width:** 9.66 IN

Weight:78 LB

Notes:All boards are varnished. Corrosion resistant. Battery included in all drives for real-time clock. Keypad kit includes HOA bypass. Keypad kit includes HOA, back reset for Europe application. EMI/RFI filters included. DC link choke included.

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Brake Chopper:** No brake chopper
- **Amperage Rating:** 14A
- **Enclosure:** IntelliDisconnect NEMA Type 1
- **Frame Size:** 5
- **Horsepower:** 10 hp
- **Software:** A
- **Voltage Rating:** 480V

Supporting documents:

- [Eaton H-Max HVAC Drives](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Size A Oversize Type 1, 12 and 3R Enclosure Outline Dims](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - HMX014A4NA](#)

Certifications:



- UL 508C
- IEC 61800-5-1
- EN 61800-5-1
- cUL Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.