



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## H-Max Drive

**HMX040A4NA**

**UPC:**786685569505

### Dimensions:

- **Height:** 13.67 IN
- **Length:** 45.45 IN
- **Width:** 11.44 IN

**Weight:**125 LB

**Notes:**All boards are varnished. Corrosion resistant. Battery included in all drives for real-time clock. Keypad kit includes HOA bypass. Keypad kit includes HOA, back reset for Europe application. EMI/RFI filters included. DC link choke included.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Brake Chopper:** No brake chopper
- **Amperage Rating:** 40A
- **Enclosure:** IntelliDisconnect NEMA Type 1
- **Frame Size:** 6
- **Horsepower:** 30 hp
- **Software:** A
- **Voltage Rating:** 480V

### Supporting documents:

- [Eaton H-Max HVAC Drives](#)
- [Eatons Volume 6-Solid-State Motor Control](#)
- [Size A Oversize Type 1, 12 and 3R Enclosure Outline Dims](#)
- [Variable frequency drive - Product overview](#)
- [Eaton Specification Sheet - HMX040A4NA](#)

### Certifications:

- IEC 61800-5-1
- UL 508C
- cUL Certified
- EN 61800-5-1

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.