



Powering Business Worldwide

pe.eaton.com

E47 Enclosed Precision Limit Switch

E47BLS12

UPC:782113959245

Dimensions:

- **Height:** 3.39 IN
- **Length:** 1 IN
- **Width:** 2.96 IN

Weight:.5125 LB

Notes:Bottom facing M4 x 0.7 (8-32) terminal screws with cup washers will accept 22 -12 AWG (2.5 sq. mm maximum)

Warranties:

- 1 year

Specifications:

- **Connection:** Screw Terminals
- **Contact Rating:** 15A at 125Vac / 15A at 14Vdc
- **Contact Configuration:** SPDT
- **Enclosure Material:** Die Cast Aluminum
- **Environmental Rating:** NEMA 1
- **Maximum Ac Current:** 15A
- **Operating Temperature:** 5° to 176°F (-15° to 80°C)
- **Switch Type:** Cross Booted Roller Plunger

Supporting documents:

- [E47 precision - Limit switches](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E47BLS12](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



