



Powering Business Worldwide

pe.eaton.com

E57 Small Diameter Series Inductive Proximity Sensor

E57EAL12T111SD

UPC:782113909103

Dimensions:

- **Height:** 1.97 IN
- **Length:** .47 IN
- **Width:** .47 IN

Weight: .06 LB

Warranties:

- 1 year

Specifications:

- **Accuracy:** < 1%
- **Connection:** 4 Pin M12 Connector
- **Contact Rating:** 200 mA at 30 Vdc
- **Contact Configuration:** PNP Open Collector, Normally Open
- **Diameter:** .47 IN
- **Enclosure Material:** Stainless Steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12 and 13 (IP67)
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red output status
- **Maximum Dc Current:** 200 mA
- **Operating Mode:** Shielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Short circuit protected
- **Sensor Type:** Inductive Proximity

Supporting documents:

- [Eaton Specification Sheet - E57EAL12T111SD](#)

Certifications: No Data

Product compliance: No Data



