



Powering Business Worldwide

pe.eaton.com

Inductive Proximity Sensor

E57LAL12A2E5

UPC:782113775234

Dimensions:

- **Height:** .47 IN
- **Length:** 2.87 IN
- **Width:** .47 IN

Warranties:

- 1 year

Specifications:

- **Type:** Inductive Proximity Sensor
- **Accuracy:** <3% sensing range
- **Contact Rating:** 250 mA at 250V
- **Cable Type:** PVC
- **Contact Configuration:** 2-wire AC, NO
- **Cord Length:** 196.8 FT
- **Enclosure Material:** 303 stainless steel
- **Environmental Rating:** NEMA 4, 4X, 6, 6P, 12, 13, IP67, IP69K
- **Input Voltage:** 20-250V
- **Led Indicators:** 360° viewable LED
- **Maximum Ac Current:** 250 mA
- **Operating Mode:** Unshielded
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Series:** E57

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E57LAL12A2E5](#)

Certifications: No Data

Product compliance: No Data



