



Powering Business Worldwide

pe.eaton.com

5P Tower UPS

5P2200

UPC:743172039637

Dimensions:

- **Height:** 3.4 IN
- **Length:** 20.6 IN
- **Width:** 17.4 IN

Weight:65 LB

Notes:Allows UPS operation without utility input

Warranties:

- 3 year on electronics, 2 year on battery

Specifications:

- **Accessories:** Tower pedestals, Quick Start Guide, Phillips head screw driver
- **Battery Type:** VRLA
- **Efficiency:** Up to 99% efficiency
- **Frequency Rating:** 40-60 Hz
- **Humidity:** 20-95% non-condensing
- **Input:** (1) 5-20P
- **Operating Temperature:** 0° to 40°C
- **Output:** (8) 5-20R
- **Topology:** Line interactive
- **User Interface:** LCD graphical display
- **Volt Ampere Rating:** 1950 KVA
- **Battery Rating:** 12V/9 Ah
- **Cable Type:** RS-232 serial cable, USB cable
- **Cord Length:** 96 FT
- **Software:** Intelligent Power Software Suite CD, User manual CD
- **Voltage Rating:** 89-151V (adj to 70-153V)
- **Wattage:** 1.92 kW
- **Color:** Black
- **Configuration:** Tower
- **Runtime:** 3 min full load, 8 min half load



Supporting documents:

- [Eaton 5P Tower UPS](#)
- [Product and Service Catalog](#)
- [Eaton Specification Sheet - 5P2200](#)

Certifications:

- UL 497A
- UL 1778
- cUL Listed

Product compliance:

- FCC Part 15 Class A Subpart B Sections
15.107b , 15.109b