



Powering Business Worldwide

pe.eaton.com

Prism Series Tubular Photoelectric Sensor

11155RA17

UPC:782113056555

Dimensions:

- **Height:** 2.55 IN
- **Length:** .47 IN
- **Width:** .71 IN

Weight:.2875 LB

Notes:Synchronous design requires source and detector to be wired to each other

Warranties:

- 3 year

Specifications:

- **Cable Type:** PVC
- **Cord Length:** 79.2 FT
- **Diameter:** .71 IN
- **Enclosure Material:** Lens: polycarbonate cable jacket: PVC body: structural polyurethane foam
- **Environmental Rating:** NEMA 1,3,4,4X,6,6P,12,13
- **Input Voltage:** 10-30 Vdc
- **Led Indicators:** Red power on
- **Operating Mode:** Thru-beam
- **Operating Temperature:** -13° to 131°F (-25° to 55°C)
- **Sensor Type:** Through Beam
- **Switch Type:** Photoelectric

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 11155RA17](#)

Certifications:

- UL Recognized
- cUL Recognized



Product compliance:

- CE Marked
- Contact Manufacturer

© 2016 Eaton. All rights reserved.