



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E51 Series, Limit Switch Style, Modular Inductive Photoelectric Sensor

**E51ALP2P3**

**UPC:**782113942810

### Dimensions:

- **Height:** 4.89 IN
- **Length:** 1.54 IN
- **Width:** 1.82 IN

**Weight:**.975 LB

### Warranties:

- 3 year

### Specifications:

- **Connection:** 3 Pin Mini Connector
- **Contact Rating:** 500 mA AC/DC Solid State Output
- **Contact Configuration:** NO or NC
- **Enclosure Material:** Receptacle and Body: Die Cast Zinc, Head: Plastic
- **Environmental Rating:** NEMA 3,3S,4,4X,6,6P,12,13, IP67
- **Input Voltage:** 20–264 Vac/dc
- **Led Indicators:** Green Power On, Amber Output Status
- **Maximum Ac Current:** 500 mA
- **Operating Mode:** Diffuse Reflective
- **Operating Temperature:** -13° to 158°F (-25° to 70°C)
- **Protection:** Latching short circuit
- **Switch Type:** Photoelectric

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E51ALP2P3](#)

**Certifications:** No Data



**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.