



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## E50 Series Limit Switch Operator

**E50KL32**

**UPC:**782113453897

### Dimensions:

- **Height:** 1.9 IN
- **Length:** .67 IN
- **Width:** .61 IN

**Weight:**.03 LB

**Notes:**Lever length is from the operating shaft axis to the tip

### Warranties:

- 1 year

### Specifications:

- **Enclosure Material:** Lever: Stainless Steel
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Operating Temperature:** -40° to 201°F (-40° to 94°C)
- **Switch Type:** Lever for Side Rotary Switches

### Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL32](#)

**Certifications:** No Data

**Product compliance:** No Data

