



Powering Business Worldwide

pe.eaton.com

E50 Series Limit Switch Operator

E50KL580

UPC:782113308746

Dimensions:

- **Height:** 2.2 IN
- **Length:** .69 IN
- **Width:** .68 IN

Weight:.05 LB

Notes:Lever length is from the operating shaft axis to the roller axis

Warranties:

- 1 year

Specifications:

- **Enclosure Material:** Lever: Stainless Steel, Roller: Steel Ball Bearing
- **Environmental Rating:** NEMA 1, 3, 3S, 4, 4X, 6, 6P, 13, IP67, IP69K
- **Operating Temperature:** -40° to 201°F (-40° to 94°C)
- **Switch Type:** Lever for Side Rotary Switches

Supporting documents:

- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - E50KL580](#)

Certifications: No Data

Product compliance: No Data

